

# STAINLESS STEEL EQUIPMENT'S







Email: sales@tavron.net Whatsapp: +91 9444015442 www.tavron.net

### Dimple Jacket



- Tanks and Reactor made out of SS304 and SS316
- The tanks will have conventional Dimple jacket, Laser Weld dimple jacket, and conventional jacket.
- The tanks will be designed with ASME code or other code on request
- The thermal duties will be well designed with computerised programme
- The tanks will be designed with process and service valves automation
- ➤ The Tanks and Reactor are designed with CIP spray ball system for on line cleaning
- PLC Control tanks and System as optional







## Limpet jacket







- > Tanks and Reactor made out of SS304 and SS316
- The tanks will have conventional limpet jacket and conventional jacket.
- ➤ The tanks will be designed with ASME code or other code on request
- ➤ The thermal duties will be well designed with computerised programme
- The tanks will be designed with process and service valves automation
- PLC Control tanks and System as optional



#### Conventional Jacket



- The Jacketed duct will be made out of SS304 and SS316
- The ducts will have Laser Weld dimple jacket for better pressure holding
- The thermal duties will be well designed with computerised programme
- The Ducts are designed with CIP retrofit nozzle system for on line cleaning
- PLC Control System as optional to control the services like steam, ice water, cooling tower water









## Vertical Storage Tank







- > PUF Insulation for better thermal stability
- > Tanks with SS 304/SS 316 Construction
- Finished to the International Standard
- Rotary Spray Ball to cover the CIP all over the tank
- > Fitted on the Legs with Adjustable Ball feet
- > Agitator with Reputed make Geared Motor
- Air Vent with Hygienic Standard
- Level Transmitter as optional
- > Temperature Transmitter & Temperature Indicator
- > Outlet with Hygienic Valves.
- Constructed with 2000 L / 3000 L / 5000 L / 10,000 L / 15,000 L



## Horizontal Storage Tank



- > Tanks with SS 304/SS 316 Construction
- > PUF Insulation for better thermal stability
- Finished to the International Standard
- Rotary Spray Ball to cover the CIP all over the tank
- Fitted on the Legs with Adjustable Ball feet
- Agitator with Reputed make Geared Motor
- Air Vent with Hygenic Standard
- > Level Transmitter as optional
- > Temperature Transmitter & Temperature Indicator
- > Outlet with Hygenic Valves.
- Single Compartment & Double Compartment
- Constructed with 2000 L/3000 L/5000 L/ 10,000 L/15,000 L/20,000 L





#### HEAD OFFICE TAVRON ENGINEERS

AF-1 Aiswariyam, 25 A Redhills Road, Kolathur, Chennai - 600 099, India. Tel:- +91 44 25567211.

Mobile: +91 9444015442. Email:- sales@tavron.net Website:www.tavron.net

#### FACTORY TAVRON ENGINEERS

38-42 Arulmurugan Nagar, Vichoor Post, Manali New Town, Chennai - 600 103. Tel: +91 9176610727.

Email: factory@tavron.net